



Clarity 6 Patch Cord, Category 6, modular 8-position to 110. Cord is terminated on one end with a male 110 plug with internal signal feedback technology, which reduces crosstalk without compromising impedance. The other cord end is terminated with an 8-position modular plug with Ortronics Paralign 2 pair isolation technology.

Features & Benefits

Verified to TIA component specifications to ensure component performance

Internal signal feedback of the 110 plug design controls noise contributors

Center tuned Paralign™ 2 modular plug design controls the plug for a transparent mated union

Assembled with premium cordage for performance, reliability and long life

Factory tested for performance to ensure consistent reliability

Specifications

General Info

Product Line	Ortronics	Color	White
UPC Number	662875455196	Country Of Origin	Mexico
Features	Standard Diameter	Application Sector	Commercial, Industrial
Standard	ANSI/TIA-568.E-2;ISO/IEC 11801-1;RoHS	Warranty Type	5-Year
Type	Copper Patch Cord		

Dimensions

Product Length US	7.0 FT	Cable Length	7 ft
-------------------	--------	--------------	------

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Operating Temperature Min	-10 °C	Category Performance Application	Cat6
Compatibility	RJ-45	Wire Gauge	22 AWG
Storage Humidity	0-90% RH (Non-Condensing)	Plating Specification	50 μ in Gold
Jacket Application	Riser Rated	Bend Radius	0.88 in
Shielded/Unshielded Cable	Unshielded	Termination Style	Pre-Terminated
Conductor Stranding	Stranded	Operating Temperature Max	60 °C
Cable Type	Non-Booted	Jacket Rating	CM Rated
Cable Diameter	0.22 in	Braid	Non-braided Wiring
Connector 2	110 Punchdown Male	Connector 1	RJ-45 Male
Operating Temperature	-10°-60°C	Operating Humidity	0-90% RH (Non-Condensing)
Number of Strands	7	Conductor Material	Copper
Voltage	300.0 V	Connectivity Footprint	Clarity
Storage Temperature	-40° - 60° C		
