



Ortronics
Clarity CAT6A Modular Patch Cord, 7 ft, White
Part No. MC6A07-09



Clarity 6A modular patch cord, white, 7', Cat6A, 10 Gigabit, four-pair UTP stranded 26 AWG PVC/CM, center tuned with Clarity connecting hardware for optimum installed performance using Ortronics Paralign 2 pair-positioning technology.

Features & Benefits

Center tuned to Clarity jacks and panels for a more transparent mated union
Narrow Paralign plug profile supports use in high density panels and hubs

Paralign™ 2 plug termination better controls plug performance

Icon compatible – provides additional TIA-606-A designation capabilities

Assembled with premium cordage, 100% factory tested for performance, reliability and long life

Specifications

General Info

Product Line	Ortronics	UPC Number	662875010784
Country Of Origin	Mexico	Application Sector	Commercial/Industrial
Standard	ANSI/TIA 568-C.2	Type	Copper Patch Cord

Dimensions

Product Length US	7.0 FT
-------------------	--------

Additional Information

RoHS Conformant	Yes	Product Environmental Profile	Yes
-----------------	-----	-------------------------------	-----