Ortronics
3FT Blue Clarity CAT6 Shielded Patch Cord
Part No. MCS603-06

Clarity® shielded patch cords utilize center tuned technology to elevate channel performance. More importantly, center tuning these cords to Clarity jacks and panels provides significant elevation of channel performance that can be field measured.

Features & Benefits

Center tuned to Clarity jacks and panels for a more transparent mated union

Narrow Paralign plug profile supports use in high density panels and hubs

Assembled with premium cordage, 100% factory tested for performance, reliability and long life

Specifications

General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875032977	Country Of Origin	Mexico
Product Type	Patch Cord	Features	Standard Diameter
Application Sector	Commercial, Industrial	Standard	ANSI/TIA-568.2-E;ISO/IEC 11801-1;RoHS
Warranty Type	5-Year		

Dimensions

Product Length US	3.0 FT	Cable Length	3 ft

Technical Information

Operating Temperature Min	-10 °C	Category Performance Application	Cat6
Compatibility	RJ-45	Wire Gauge	24 AWG
Storage Humidity	0-90% RH (Non-Condensing)	Plating Specification	50 µ in Gold
Jacket Application	Riser Rated	Bend Radius	0.98 in

Shielded/Unshielded Cable	Shielded	Termination Style	Pre-Terminated
Conductor Stranding	Solid	Operating Temperature Max	60 °C
Cable Type	Non-Booted	Jacket Rating	CM Rated
Cable Diameter	0.245 in	Braid	Non-braided Wiring
Connector 2	RJ-45 Male	Connector 1	RJ-45 Male
Operating Temperature	-10°-60°C	Operating Humidity	0-90% RH (Non-Condensing)
Number of Strands	7	Conductor Material	Copper
Voltage	300.0 V	Connectivity Footprint	Clarity
Storage Temperature	-40° - 60° C		