



Ortronics
Clarity CAT6A Shielded Patch Cord, 9', Gray
Part No. MCS6A09-08



Clarity 6A FTP Modular Patch Cord, gray, 9', Category 6A, four-pair FTP stranded 26 AWG PVC/CM, center tuned with Clarity 6 A connecting hardware for optimum Category 6A installed performance using Shielded Paralign 2 pair-positioning technology.

Features & Benefits

Center tuned to Clarity jacks and panels for a more transparent mated union:

Icon compatible – provides additional TIA-606-A designation capabilities:

Paralign™ 2 plug termination better controls plug performance:

Narrow Paralign plug profile supports use in high density panels and hubs:

Assembled with premium cordage, 100% factory tested for performance, reliability and long life

Assembled with premium cordage, 100% factory tested for performance, reliability and long life

Specifications

General Info

Product Line	Ortronics	Color	Gray
UPC Number	662875877899	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Standard	ETL
Warranty Type	5-Year	Type	Copper Patch Cord

Dimensions

Product Length US	9.0 FT	Cable Length	9 ft
-------------------	--------	--------------	------

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Jacket Material	PVC	Operating Temperature Min	-10 °C
Category Performance Rating	Cat6a	Wire Gauge	26 AWG
Storage Humidity	0-90% RH (Non-Condensing)	Plating Specification	50 μ in Gold
Jacket Application	Riser Rated	Bend Radius	0.98 in
Shielded/Unshielded	Shielded	Termination Style	Pre-Terminated
Conductor Stranding	Solid	Operating Temperature Max	60 °C
Jacket Rating	CM Rated	Cable Diameter	0.245 in
Braid	Non-braided Wiring	Operating Temperature	-10°-60°C
Operating Humidity	0-90% RH (Non-Condensing)	Conductor Material	Copper
Voltage	300.0 V	Storage Temperature	-40° - 60° C