



Pass and Seymour  
Discontinued - Midget Flanged Inlet - Black Face, Gray Flange  
Part No. ML215

Midget Lock Flanged Inlet 2-Pole 3-Wire 15A 125A



## Features & Benefits

Quality Materials, durability, and time-tested design

Wire Size: 18/3 thru 14/3 AWG Round cord (.23" - .52" Dia.)

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	Mexico	Application Sector	Commercial/Industrial
Standard	UL Listed		

### Dimensions

Product Width US	2.06 in	Product Depth US	1.13 in
------------------	---------	------------------	---------

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes
------------	-----

### Technical Information

Phase	Single	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Wire Size	18 - 14 AWG	Voltage	125.0 V

---

Environmental Conditions      UL94 V2, Maximum Continuous +75°C,  
minimum -40°C without impact

---