



The mighty mo 20 channel racks are designed to provide the greatest in cable management flexibility and efficiency. Honeycomb cutout sidewall allow for infinite cable pathways. The universal 3/8" square hole punch enables mounting of all standard cage nuts and OEM quick mount slides and rails. This creates the industries most versatile equipment rack system.

Features & Benefits

Many option for all applications: 5 depths, square hole or tapped hole configurations

Built-in top trough with waterfalls: Gives bend radius control and cable routing.

Speed nuts included: Increases speed and ease of assembly, while adding extra strength to your rack-- Speednut eliminates the need for a second wrench.

Cablofil® ready cable tray & runway brackets

Honeycomb side rails designed to maximize the airflow of network equipment: Combined with baffles, manages intake and exhaust air creating cold aisle/hot aisle distribution from side vented equipment.

Vertical management solutions: A solution for every application- cage with rack unit fingers & hinged slam latch door, cage with rack unit fingers & snap-on covers, cage with hinged latches, and individual cable management rings.

Can be assembled as a 19" or 23" rack: No additional hardware required- no need to stock two sizes of racks.

Easy Installation: Mighty Mo 20 Racks can assemble in less than 15 minutes/rack

Rack includes hardware kit, two packages of hook and loop D-style straps and 50 #12-24 equipment mounting screws: Do not have to purchase as separate items- money saving.

delete

Specifications

General Info

Product Line	Ortronics	Color	White
Finish	Powder Coat	UPC Number	662875836537
Country Of Origin	United States	Material	Steel
Included	Hardware for mounting	Application Sector	Commercial

Warranty Type	5-Year	Type	Rack
Dimensions			
Product Width US	23.75 in	Product Weight US	46.0 lb
Product Depth US	24.0 in	Product Height US	86.0 in
Rack Depth	34 in		
Additional Information			
RoHS Compliant	Yes	Energy Savings	No
Product Environmental Profile	Yes		
Technical Information			
Compatibility	Mighty Mo	Rack Units	45 U
Mounting Hole Type	Punched, 3/8 in Square	Mounting Rail Spacing	19 in
Load Capacity	2000 lb	Cable Entry	Back, Front
Frame	Channel	Mounting	Floor