Ortronics

MM20 Channel Rack, 30" deep, 7 ft, 45 RU, tapped, Black

Part No. MM20730-B

Mighty Mo 20 channel racks are designed to provide greater flexibility and optimum efficiency to any size network. The top trough with built-in waterfall provides bend radius control and efficient patch cable routing. Honeycomb side rails on all depth channel racks provide the ultimate in distribution cable management. The honeycomb side rails, combined with airflow baffles, create a patented system that manages intake and exhaust air from side-vented equipment.

Features & Benefits

Many option for all applications: 5 depths, square hole or tapped hole configurations

Built-in top trough with waterfalls: Gives bend radius control and cable routing.

Speed nuts included: Increases speed and ease of assembly, while adding extra strength to your rack--Speednut eliminates the need for a second wrench.

Cablofil® ready cable tray & runway brackets

Honeycomb side rails designed to maximize the airflow of network equipment: Combined with baffles, manages intake and exhaust air creating cold aisle/hot aisle distribution from side vented equipment.

Vertical management solutions: A solution for every application-cage with rack unit fingers & hinged slam latch door, cage with rack unit fingers & snap-on covers, cage with hinged latches, and individual cable management rings.

Can be assembled as a 19" or 23" rack: No additional hardware required- no need to stock two sizes of racks.

Easy Installation: Mighty Mo 20 Racks can assemble in less than 15 minutes/rack

Rack includes hardware kit, two packages of hook and loop D-style straps and 50 #12-24 equipment mounting screws: Do not have to purchase as separate items- money saving.

Specifications

General Info

Product Line	Ortronics	Color	Black
Finish	Powder Coat	UPC Number	662875214823
Country Of Origin	Mexico	Material	Aluminum
Product Type	Open Frame Rack	Included	Hardware for mounting

Application Sector	Commercial	Standard	UL 2416
Warranty Type	5-Year		

Dimensions

Product Width US	23.75 in	Product Weight US	50.75 lb
Product Depth US	40.0 in	Product Height US	86.0 in
Rack Depth	40 in		

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes

Technical Information

Compatibility	Mighty Mo	Rack Units	45 U
Mounting Hole Type	Tapped	Mounting Rail Spacing	19 in
Load Capacity	2000 lb	Cable Entry	Back, Front
Frame	Channel	Mounting	Floor