



Mighty Mo 20 4-post racks provide greater flexibility and optimum efficiency in any data center. The adjustable rack allows all 4 mounting rails to be adjusted even after the rack has been fastened to the floor. Front and rear waterfalls allow for equipment patching and server patching. All styles of Mighty Mo 20 vertical managers can be mounted front or rear and airflow baffles can be mounted to manage the airflow of side breathing equipment.

### Specifications

#### General Info

Color	Black	UPC Number	662875949008
Country Of Origin	United States	Product Line	Legrand
Application Sector	Commercial	Type	Rack
Standard	UL 2416		

#### Additional Information

RoHS Conformant	Yes
-----------------	-----

#### Technical Information

Static Load Capacity	2000 lbs.	Rack Units	45U
----------------------	-----------	------------	-----