



Mighty Mo 20 4-post adjustable racks are allows all 4 mounting rails to be adjusted even after the rack has been fastened to the floor. Available in depths of 30", 36" & 42" depths in both square hole cage nut styles or threaded rails. Front and rear waterfalls allow for equipment patching and server patching. All styles of Mighty Mo 20 vertical managers can be mounted front or rear and airflow baffles can be mounted to manage the airflow of side breathing equipment.

Features & Benefits

| | |
|--|--|
| Large selection of Channel and 4-Post racks | All 4 mounting rails to be adjusted even after the rack has been fastened to the floor |
| Front and rear waterfalls allow for equipment patching and server patching | Static capacity 2,000 lbs |
| Threaded hole and square hole punch available on all channel and 4 post racks | Deeper waterfall for increased cable capacity |
| Rack includes two packages of hook and loop D-style straps and 50 #12-24 cage nuts and screws, do not have to purchase as separate items; money saving | |

Specifications

General Info

| | | | |
|--------------------|--------------|-------------------|---------------|
| Product Line | Ortronics | Color | White |
| UPC Number | 662875216544 | Country Of Origin | United States |
| Application Sector | Commercial | Type | Rack |

Dimensions

| | | | |
|------------------|----------|-------------------|----------|
| Product Width US | 23.75 in | Product Weight US | 55.52 lb |
| Product Depth US | 46.0 in | Product Height US | 86.0 in |

Additional Information

| | | | |
|-----------------|-----|-------------------------------|-----|
| RoHS Conformant | Yes | Product Environmental Profile | Yes |
|-----------------|-----|-------------------------------|-----|