



Ortronics
Mighty Mo 20 Adjustable 4-Post Rack, 42"D Adjustable, 7'H, 45 RU, Square Hole Rails, Black
Part No. MM20742ADJ38-B



Mighty Mo 20 4-post adjustable racks are allows all 4 mounting rails to be adjusted even after the rack has been fastened to the floor. Availble in depths of 30", 36" & 42" depths in both square hole cage nut styles or threaded rails. Front and rear waterfalls allow for equipment patching and server patching. All styles of Mighty Mo 20 vertical managers can be mounted front or rear and airflow baffles can be mounted to manage the airflow of side breathing equipment.

Features & Benefits

Large selection of Channel and 4-Post racks	All 4 mounting rails to be adjusted even after the rack has been fastened to the floor
Front and rear waterfalls allow for equipment patching and server patching	Static capacity 2,000 lbs
Threaded hole and square hole punch available on all channel and 4 post racks	Deeper waterfall for increased cable capacity
Deeper waterfall for increased cable capacity	Rack includes two packages of hook and loop D-style straps and 50 #12-24 cage nuts and screws, do not have to purchase as separate items; money saving

Specifications

General Info

Product Line	Ortronics	Color	Black
Finish	Powder Coat	UPC Number	662875214885
Country Of Origin	United States	Material	Steel
Features	Adjustable Rail Spacing, Square Holes	Included	Hardware for mounting
Application Sector	Commercial	Warranty Type	5-Year
Type	Rack		

Dimensions

Product Width US	23.75 in	Product Weight US	80.0 lb
Product Depth US	42.0 in	Product Height US	85.25 in
Rack Depth	42 in		

Additional Information

RoHS Compliant	Yes	Energy Savings	No
----------------	-----	----------------	----

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Compatibility	Mighty Mo	Rack Units	45 U
---------------	-----------	------------	------

Mounting Hole Type	Punched, 3/8 in Square	Mounting Rail Spacing	19 in
--------------------	------------------------	-----------------------	-------

Load Capacity	2000 lb	Cable Entry	Back, Front
---------------	---------	-------------	-------------

Frame	Adjustable	Mounting	Floor
-------	------------	----------	-------
