



The mighty mo 20 channel racks are designed to provide the greatest in cable management flexibility and efficiency. Honeycomb cutout sidewall allow for infinite cable pathways. The universal 3/8" square hole punch enables mounting of all standard cage nuts and OEM quick mount slides and rails. This creates the industries most versatile equipment rack system.

Features & Benefits

Many option for all applications: 5 depths, square hole with rack unit fingers or tapped hole configurations	Vertical management solutions: A solution for every application-cage with rack unit fingers & hinged slam latch door, cage with rack unit fingers & snap-on covers, cage with hinged latches, and individual cable management rings.
Built-in top trough with waterfalls: Gives bend radius control and cable routing.	Can be assembled as a 19" or 23" rack: No additional hardware required- no need to stock two sizes of racks.
Speed nuts included: Increases speed and ease of assembly, while adding extra strength to your rack-- Speednut eliminates the need for a second wrench.	Easy Installation: Mighty Mo 20 Racks can assemble in less than 15 minutes/rack
Large range of accessories	Cablofil® ready cable tray & runway brackets
Rack includes hardware kit, two packages of hook and loop D-style straps and 50 #12-24 equipment mounting screws: Do not have to purchase as separate items- money saving.	Honeycomb side rails designed to maximize the airflow of network equipment: Combined with baffles, manages intake and exhaust air creating cold aisle/hot aisle distribution from side vented equipment.
Open channels top and bottom: Allows floor and ceiling access for horizontal distribution cables.	

Specifications

General Info

Product Line	Ortronics	Color	White
UPC Number	662875836414	Country Of Origin	United States
Application Sector	Commercial	Type	Rack

Dimensions

Product Width US	23.75 in	Product Weight US	42.56 lb
Product Depth US	26.25 in	Product Height US	98.0 in

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----