



The wire frame and rack unit finger design promotes efficient routing of patch cords between racks. Dual hinged slam latch doors allow easy access during moves, adds and changes. Supplied with four cable management spools to provide slack storage for fiber jumpers and twelve bend limiting clips to protect fiber entering the vertical manager.

Features & Benefits

Accepts 180°Bend limiting clips for fiber access	Bottom support to eliminate sag and step issues
Clean aesthetic look	Spring loaded actuator on handles for smooth opening and closing
Left or right hinge and removable door.	2" deeper fingers for higher density networks
Deeper vertical managers with up to 40% more room	Strong flexible fingers
Larger capacity, including longer finger sections	

Specifications

General Info

Product Line	Ortronics	Color	White
Finish	Powder Coat	UPC Number	662875218357
Country Of Origin	United States	Included	Mounting Hardware
Application Sector	Commercial	Warranty Type	5-Year
Type	Rack		

Dimensions

Product Width US	12.25 in	Product Weight US	59.94 lb
Product Depth US	15.0 in	Product Height US	89.0 in

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Compatibility	Mighty Mo	Rack Units	51
---------------	-----------	------------	----

Seismic Tested	No	Mounting	Vertical
----------------	----	----------	----------
