



The P600 is designed for the international DIN rail mounting standard which is heavily adopted throughout Europe. It gives any room instant access to endless music options from networked collections or a variety of internet radio and streaming services - all from a single, intuitive app. The P600 supplies 2x20 watts of efficient Class D digital amplification for a single zone of powerful audio.

The P600 is powered by the P601 DIN Rail Power Supply. The P601 is designed to power up to four P600 DIN Rail Players, making the system scalable and easy to expand in up to 16 zones.

Check out the [Player Portfolio mobile app](#).

Features & Benefits

Convenient control is always at hand with intuitive Nuvo Player app for iOS and Android mobile devices	Convenient control options using the Nuvo Player app, optional in-wall keypads, and on-wall touch screens
Designed specifically for the international DIN rail mounting standard	DIN Rail Mounting
Efficient Class D amplifiers provide 40 watts of power at 8 ohms to a single zone	Give any room endless music options with built-in access to networked audio content and streaming services : Spotify, Pandora, iHeartRadio, TuneIn, Napster, Deezer, and SiriusXM
Instant access to networked audio content and streaming services – Spotify, Pandora, Amazon Music, iHeartRadio, TuneIn, Napster, Deezer, and SiriusXM	Optional in-wall Keypads and Touch Screen provide a fixed-location control point
Seamless integration into advanced automation systems from KNX, Vantage, Control4, RTI, and more	Cat 5e minimum; Line Input Connector: 3mm stereo; Speaker Output Connection: screw-down; USB Connection Network Connectivity: RJ45

Specifications

General Info

Product Line	Nuvo	Color	Cement
Hazardous Materials	No	UPC Number	701963860013
Country Of Origin	China	Application Sector	Residential

Standard	cTUVus, CE-LVD; US:FCC CFR Title 47 Part 15, Subpart B; CANADA:ICES-003; EUROPE:CISPR13; EUROPE: 55020; AUSTRALIA/NEW ZEALAND: C-TICK standard AS/NZS CISPR13; RoHS (Restriction of Hazardous Substances Directive 2002/95/EC	Type	DIN Rail Player
----------	---	------	-----------------

Technical Information

Power Supply	24 VDC External	Output Power	40 W
Input Voltage	24 VDC	Damping Factor	50+
Number of Fibers	Line Input Connector: 3mm stereo Speaker Output Connection: screw-down USB Connection Network Connectivity: RJ45, Cat 5e minimum		