



Nuvo
Discontinued - Nuvo P600 4-Zone DIN Rail Player
Part No. NVP6004ZNA



The Nuvo DIN Rail Player is a first of its kind streaming audio player meant specifically to be mounted on a standard DIN Rail. With performance and features most equal to the well known Nuvo P100 Player the Nuvo DIN Rail Player facilitates ease of installation where DIN Rail is the accepted standard for mounting of electrical, network, and like devices in the project. This kit includes everything needed for a three zone installation. It includes four (4) NV-P600 DIN Rail Players, two 1/2 width DIN rails for low-voltage plastic enclosure mounting of up to six (6) NV-P600 DIN Rail Players, six (6) DC power cables, two (2) 1 input 3 output DC power cable splitter, two (2) PW1060 24 volt DC power supplies, each of which is capable of powering up to 3 individual Nuvo NV-P600 DIN Rail Players, four (4) 12" CAT5e patch cables, one (1) 36" CAT5e patch cables.

Features & Benefits

Cat 5e minimum; Line Input Connector: 3mm stereo; Speaker Output Connection: screw-down; USB Connection Network Connectivity: RJ45

Specifications

General Info

Product Line	Nuvo	UPC Number	701963860709
Country Of Origin	China	Application Sector	Residential
Standard	cTUVus, CE-LVD; US:FCC CFR Title 47 Part 15, Subpart B; CANADA:ICES-003; EUROPE:CISPR13; EUROPE: 55020; AUSTRALIA/NEW ZEALAND: C-TICK standard AS/NZS CISPR13; RoHS (Restriction of Hazardous Substances Directive 2002/95/EC	Type	DIN Rail Player

Technical Information

Power Supply	24 VDC External	Output Power	40 W
Input Voltage	24 VDC	Damping Factor	50+
Number of Fibers	Line Input Connector: 3mm stereo Speaker Output Connection: screw-down USB Connection Network Connectivity: RJ45, Cat 5e minimum	Mounting	DIN Rail