



Q-Series OFP Standard Density Adapter Panels offer pass-through connections and front-loading access for Q-Series Enclosures. Compatible with Q-Series Rack Mount or Wall Mount Fiber Enclosures.

Features & Benefits

Up to 72 LC fibers per RU

Available in, LC, SC, ST and blank styles

Made of durable polycarbonate

Zirconia ceramic sleeves for optimal performance

6, 8, 12 & 24 port panels

Color options available

Utilizes Shuttered Adapters

Specifications

General Info

Product Line	Ortronics	Color	Aqua
UPC Number	662875981350	Country Of Origin	Mexico
Material	Thermoplastic	Features	Shuttered
Included	Cover	Application Sector	Commercial, Data Center
Standard	RoHS compliant. Meets or exceeds TIA/EIA-568-C.3 requirements.	Warranty Type	5-Year
Type	Adapter Panel		

Dimensions

Product Width US	5.12 in	Product Depth US	1.15 in
Product Height US	1.19 in		

Technical Information

Fiber Optic Cable Type	OM3, OM4	Operating Temperature Min	-10 °C
Compatibility	OFB	Number of Ports	16
Alignment Sleeve Material	Zirconia	Simplex/Duplex	Quad
Operating Temperature Max	60 °C	Shuttered Adapters	No
Single/Multimode	Multimode	Number of Fibers	16
Connector 2	MTP	Connector 1	LC Female
Performance Level/Tier	Ultra	Operating Temperature	-10°-60°C
Durability	500 matings	Operating Humidity	0-80% RH (Non-Condensing)
Connectivity Footprint	Q-Series Standard Density	Storage Temperature	-40° - 75° C
