Ortronics

6-MPO single mode green feed-through adapters, type A

Part No. OFP-MPA72CA

The Ortronics OptiMo® OFP series adapter panels are used with our popular FC Series modular fiber cabinets, offering great flexibility in structured cabling design. Front-removable adapter panels are available with LC, SC, ST, and MT-RJ adapters and feature options ideal for both single mode and multimode applications.

Features & Benefits

Multiple Color options available: Red, Green, Beige, Aqua

Fiber port labeling: Provides fiber port identification for easier administration

Plunger/grommet fasteners: Quick and easy insertion and removal

Specifications

General Info

Product Line	Ortronics	Color	Green
UPC Number	662875631828	Country Of Origin	Mexico
Material	Steel	Product Type	Adapter Panel
Features	Toolless Installation	Included	Cover
Application Sector	Commercial, Data Center	Standard	TIA-568-C.3;RoHS Compliant
Warranty Type	5-Year		

Dimensions

Product Width US	5.12 in	Product Depth US	0.78 in
Product Height US	1.19 in		

Additional Information

Product Environmental Profile	Yes

Technical Information

Fiber Optic Cable Type	OS2	Operating Temperature Min	-10 °C
Compatibility	Q-Series SD Enclosure, RFP SD Panels	Number of Ports	72
Alignment Sleeve Material	Zirconia	Simplex/Duplex	Duplex
Polarity Type	A	Operating Temperature Max	60 °C
Single/Multimode	Single-Mode	Number of Fibers	72
Connector 2	MPO Female	Connector 1	MPO Female
Operating Temperature	-10°-60°C	Durability	500 matings
Operating Humidity	0-80% RH (Non-Condensing)	Connectivity Footprint	Q-Series Standard Density
Storage Temperature	-40° - 75° C		