



Ortronics fiber adapter panel allows for flexibility and expansion with an industry accepted style. The adapter panel snaps in for installation and can be removed easily for future changes. The adapter panel is silkscreened for easy port identification.

## Features & Benefits

Up to 72 LC fibers per RU

Available in, LC, SC, ST and blank styles

Made of durable polycarbonate

Zirconia ceramic sleeves for optimal performance

6, 8, 12 & 24 port panels

Color options available

## Specifications

### General Info

Product Line	Ortronics	Color	Aqua
UPC Number	662875629221	Country Of Origin	Mexico
Features	Toolless Installation	Included	Cover
Application Sector	Commercial, Data Center	Standard	RoHS compliant. Meets or exceeds TIA/EIA-568-C.3 requirements.
Warranty Type	5-Year	Type	Adapter Panel

### Dimensions

Product Width US	5.12 in	Product Depth US	1.43 in
Product Height US	1.19 in		

### Technical Information

Fiber Optic Cable Type	OS2	Operating Temperature Min	-10 °C
Compatibility	OFP	Number of Ports	8

Simplex/Duplex	Duplex	Operating Temperature Max	60 °C
Shuttered Adapters	No	Single/Multimode	Multimode
Connector 2	ST Female	Connector 1	ST Female
Form Factor	SC Duplex	Operating Temperature	-10°-60°C
Operating Humidity	0-80% RH (Non-Condensing)		