



Ortronics
Q-Series Keyed OFP Adapter Panel 4-SC-Duplex Aqua Adapters
Part No. OFP-SCD08LC



Ortronics fiber adapter panel allows for flexibility and expansion with an industry accepted style. The adapter panel snaps in for installation and can be removed easily for future changes. The adapter panel is silkscreened for easy port identification.

Features & Benefits

- Up to 72 LC fibers per RU
- Made of durable polycarbonate
- 6, 8, 12 & 24 port panels
- Utilizes Shuttered Adapters
- Available in, LC, SC, ST and blank styles
- Zirconia ceramic sleeves for optimal performance
- Color options available

Specifications

General Info

Product Line	Ortronics	Color	Aqua
UPC Number	662875629221	Country Of Origin	Mexico
Material	Thermoplastic	Features	Toolless Installation
Included	Cover	Application Sector	Commercial, Data Center
Standard	RoHS compliant. Meets or exceeds TIA/EIA-568-C.3 requirements.	Warranty Type	5-Year
Type	Adapter Panel		

Dimensions

Product Width US	5.12 in	Product Depth US	1.43 in
Product Height US	1.19 in		

Technical Information

Fiber Optic Cable Type	OS2	Operating Temperature Min	-10 °C
Compatibility	OFP	Number of Ports	8
Alignment Sleeve Material	Zirconia	Simplex/Duplex	Duplex
Operating Temperature Max	60 °C	Shuttered Adapters	No
Single/Multimode	Multimode	Number of Fibers	8
Connector 2	ST Female	Connector 1	ST Female
Form Factor	SC Duplex	Operating Temperature	-10°-60°C
Durability	500 matings	Operating Humidity	0-80% RH (Non-Condensing)
Connectivity Footprint	Q-Series Standard Density	Storage Temperature	-40° - 75° C
