



Ortronics fiber adapter panel allows for flexibility and expansion with an industry accepted style. The adapter panel snaps in for installation and can be removed easily for future changes. The adapter panel is silkscreened for easy port identification.

Features & Benefits

- Small footprint: Up to 72 LC fibers per RU

Plunger/grommet fasteners: Made of durable polycarbonate

Fiber port labeling: 6, 8, 12 & 24 port panels
- Adapter panels available with a wide variety of configurations: Available in, LC, SC, ST and blank styles

Front loading: Zirconia ceramic sleeves for optimal performance

Engineered polymer adapter panel: Color options available

Specifications

General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875593881	Country Of Origin	Mexico
Application Sector	Commercial	Warranty Type	5-Year
Type	Adapter Panel		

Dimensions

Product Width US	5.12 in	Product Depth US	1.43 in
Product Height US	1.19 in		

Technical Information

Fiber Optic Cable Type	OS2	Number of Ports	12
Simplex/Duplex	Duplex	Single/Multimode	Single-Mode
Form Factor	SC Duplex		