



Ortronics fiber adapter panel allows for flexibility and expansion with an industry accepted style. The adapter panel snaps in for installation and can be removed easily for future changes. The adapter panel is silkscreened for easy port identification

Features & Benefits

Up to 72 LC fibers per RU

Available in, LC, SC, ST and blank styles

Made of durable polycarbonate

Zirconia ceramic sleeves for optimal performance

6, 8, 12 & 24 port panels

Color options available

Utilizes Shuttered Adapters

Specifications

General Info

Product Line	Ortronics	Color	Red
UPC Number	662875594741	Country Of Origin	Mexico
Material	Thermoplastic	Features	Toolless Installation
Included	Cover	Application Sector	Commercial, Data Center
Standard	RoHS compliant. Meets or exceeds TIA/EIA-568-C.3 requirements.	Warranty Type	5-Year
Type	Adapter Panel		

Dimensions

Product Width US	5.12 in	Product Depth US	1.1 in
------------------	---------	------------------	--------

Product Height US	1.19 in
-------------------	---------

Technical Information

Fiber Optic Cable Type	OS2	Operating Temperature Min	-10 °C
------------------------	-----	---------------------------	--------

Compatibility	OFP	Number of Ports	6
---------------	-----	-----------------	---

Alignment Sleeve Material	Zirconia	Simplex/Duplex	Duplex
---------------------------	----------	----------------	--------

Operating Temperature Max	60 °C	Single/Multimode	Single-Mode
---------------------------	-------	------------------	-------------

Number of Fibers	6	Connector 2	ST Female
------------------	---	-------------	-----------

Connector 1	ST Female	Operating Temperature	-10°-60°C
-------------	-----------	-----------------------	-----------

Durability	500 matings	Operating Humidity	0-80% RH (Non-Condensing)
------------	-------------	--------------------	---------------------------

Connectivity Footprint	Q-Series Standard Density	Storage Temperature	-40° - 75° C
------------------------	---------------------------	---------------------	--------------
