



Cablofil
Discontinued - SC-A457-0012-12 G 4"H SOLID TRAY 12'L 12"W
Part No. P012906



Choose from an extensive selection of metallic ladder tray with a variety of rung and bottom styles to choose from. Rail heights range from 4" to 7" and width sizes are available up to 36".

Features & Benefits

Material: Commercial Quality Steel / ASTM A-1008 / A-1011

Finish: Ho-dip Galvanized after Fabrication / ASTM A-123

Bottom: Ldr: 1" wide + rung SC: Solid Corrugated VC: Vented Corrugated

Construction: Welded

Tray Design: Tray construction and markings are per the latest edition of NEMA Standards Publication VE1, CSA C22.2 No. 126

Tray Grounding Capability: Classified as an equipment grounding conductor per NEC 392.60

Specifications

General Info

Product Line	Cablofil	Finish	Hot Dipped Galvanized after Fabrication
UPC Number	800388268012	Country Of Origin	Mexico
Bottom Type	Solid Corrugated	Application Sector	Commercial, Industrial
Type	Straight Sections		

Dimensions

Product Width US	12.0 in	Product Weight US	540.0 lb
Product Volume US	4.0 cu ft	Product Depth US	144.0 in
Product Height US	4.0 in		

Trade Programs

BAA	Yes
-----	-----

Technical Information

NEMA Load Class	12C
-----------------	-----
