



Cable cleats provide a more robust and secure method to safely fasten cable to cable tray rungs than cable ties.

Features & Benefits

For trefoil formation applications

Heavy duty 316L stainless steel construction

Short circuit rating of 140kA peak fault

Third party certification to IEC 61914

Securely clamps around 1" rungs for maximum strength, fasteners included

Liners are classified as low smoke & fume, zero halogen and phosphorus-free

Bolt collar provides positive stop to avoid over tightening

Operating temperature -60°C to +60°C

Protects against damage to cables and ladder tray in the event of a short circuit

Specifications

General Info

Product Line	Cablofil	Finish	Other
UPC Number	800388536746	Country Of Origin	United Kingdom
Type	Accessories		

Dimensions

Product Width US	3.31 in	Product Weight US	1.148 lb
Product Volume US	0.025 cu ft	Product Depth US	2.13 in
Product Height US	6.1 in		

Technical Information

Maximum Cable Range

1.38 in

Minimum Cable Range

1.18 in
