



Cable cleats provide a more robust and secure method to safely fasten cable to cable tray rungs than cable ties.

Features & Benefits

For trefoil formation applications	Heavy duty 316L stainless steel construction
Short circuit rating of 140kA peak fault	Third party certification to IEC 61914
Securely clamps around 1" rungs for maximum strength, fasteners included	Liners are classified as low smoke & fume, zero halogen and phosphorus-free
Bolt collar provides positive stop to avoid over tightening	Operating temperature -60°C to +60°C
Protects against damage to cables and ladder tray in the event of a short circuit	

Specifications

General Info

Product Line	Cablofil	Finish	Other
UPC Number	800388536753	Country Of Origin	United Kingdom
Type	Accessories		

Dimensions

Product Width US	3.43 in	Product Weight US	1.188 lb
Product Volume US	0.027 cu ft	Product Depth US	2.13 in
Product Height US	6.34 in		

Technical Information

Maximum Cable Range

1.5 in

Minimum Cable Range

1.3 in