



Cable cleats provide a more robust and secure method to safely fasten cable to cable tray rungs than cable ties.

Features & Benefits

For trefoil formation applications

Short circuit rating of 140kA peak fault

Securely clamps around 1" rungs for maximum strength, fasteners included

Bolt collar provides positive stop to avoid over tightening

Protects against damage to cables and ladder tray in the event of a short circuit

Heavy duty 316L stainless steel construction

Third party certification to IEC 61914

Liners are classified as low smoke & fume, zero halogen and phosphorus-free

Operating temperature -60°C to +60°C

Specifications

General Info

Product Line	Cablofil	Finish	Other
UPC Number	800388536920	Country Of Origin	United Kingdom
Type	Accessories		

Dimensions

Product Width US	9.84 in	Product Weight US	2.715 lb
Product Volume US	0.149 cu ft	Product Depth US	2.13 in
Product Height US	12.32 in		

Technical Information

Maximum Cable Range

4.69 in

Minimum Cable Range

4.37 in
