



Cablofil
09-4A12C-S144-06 AL 4H LDR 9RS 144L 06W (TRA)
Part No. P300128



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

Features & Benefits

Material: Aluminum Alloy 6063-T6

Finish: Plain

Bottom: Ldr: 1" wide I rung SB: Flat Sheet over 12" Rung Spacing.
SC: Solid Corrugated VC: Vented Corrugated

Construction: Welded

Tray Design: Tray construction and markings are per the latest edition of NEMA Standards Publication VE1, CSA C22.2 No. 126.

Tray Grounding Capability: Classified as an equipment grounding conductor per NEC 392.60.

Specifications

General Info

Product Line	Cablofil	Finish	AL
UPC Number	800388059931	Country Of Origin	Mexico

Dimensions

Product Width US	7.5 in	Product Weight US	18.288 lb
Product Volume US	2.588 cu ft	Product Depth US	144.0 in
Product Height US	4.14 in		

Buy American Act Compliance

BAA	Yes
-----	-----