



Cablofil
09-4A12C-S144-36 AL 4H LDR 9RS 144L 36W (TRA)
Part No. P300134



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

Features & Benefits

Material: Aluminum Alloy 6063-T6

Finish: Plain

Bottom: Ldr: 1" wide I rung SB: Flat Sheet over 12" Rung Spacing.
SC:Solid Corrugated VC: Vented Corrugated

Construction: Welded

Tray Design: Tray construction and markings are per the latest edition of NEMA Standards Publication VE1, CSA C22.2 No. 126.

Tray Grounding Capability: Classified as an equipment grounding conductor per NEC 392.60.

Specifications

General Info

| | | | |
|--------------------|-----------------------|-------------------|---------------|
| Product Line | Cablofil | Finish | AL |
| UPC Number | 800388059993 | Country Of Origin | Mexico |
| Application Sector | Commercial/Industrial | Standard | UL Classified |
| Type | Cable Tray | | |

Dimensions

| | | | |
|-------------------|--------------|-------------------|-----------|
| Product Width US | 37.5 in | Product Weight US | 30.208 lb |
| Product Volume US | 12.938 cu ft | Product Depth US | 144.0 in |
| Product Height US | 4.14 in | | |

Buy American Act Compliance

BAA

Yes
