



Cablofil  
4" Itray Aluminum Straight Sections  
Part No. P300155



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

## Features & Benefits

Material: Aluminum Alloy 6063-T6

Finish: Plain

Bottom: Ldr: 1" wide I rung SB: Flat Sheet over 12" Rung Spacing.  
SC: Solid Corrugated VC: Vented Corrugated

Construction: Welded

Tray Design: Tray construction and markings are per the latest edition of NEMA Standards Publication VE1, CSA C22.2 No. 126.

Tray Grounding Capability: Classified as an equipment grounding conductor per NEC 392.60.

## Specifications

### General Info

Product Line	Cablofil	Finish	Aluminum
UPC Number	800388060203	Country Of Origin	Mexico
Bottom Type	Ladder	Application Sector	Commercial, Industrial
Type	Straight Sections		

### Dimensions

Product Width US	37.5 in	Product Weight US	26.772 lb
Product Volume US	12.938 cu ft	Product Depth US	144.0 in
Product Height US	4.14 in	Rung Spacing	12 in

## Trade Programs

BAA	Yes
-----	-----

Technical Information

NEMA Load Class	12C
-----------------	-----