



Cablofil  
4A-DIV-90VO12-S6 DIVIDER 4H 90° OVR 12R (TRA)  
Part No. P319048



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

## Features & Benefits

Material: Aluminum

Each divider includes two self-drilling screws

## Specifications

### General Info

Product Line	Cablofil	Finish	Aluminum
UPC Number	800388468153	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Type	Vertical Other

### Dimensions

Product Width US	0.49 in	Product Weight US	0.65 lb
Product Volume US	0.101 cu ft	Product Depth US	18.842 in
Product Height US	18.842 in	Radius	12 in

### Trade Programs

BAA	Yes
-----	-----