



Cablofil
6A-DIV-90VO24-S6 DIVIDER 6H 90° OVR 24R (TRA)
Part No. P319073



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

Features & Benefits

Material: Aluminum

Each divider includes two self-drilling screws

Specifications

General Info

Product Line	Cablofil	Finish	Aluminum
UPC Number	800388468207	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Type	Vertical Other

Dimensions

Product Width US	0.49 in	Product Weight US	2.292 lb
Product Volume US	0.306 cu ft	Product Depth US	32.842 in
Product Height US	32.842 in	Radius	24 in

Trade Programs

BAA	Yes
-----	-----