



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

Features & Benefits

Material: Steel

Load Rating: 1,200 lbs/pr (S.F.: 3X)

Finishes: ZN, PE, GC, 316L

Threaded Rod Size: 3/8" or 1/2"

Width: 1-1/2"

Kit Includes: 8 SFHN

Specifications

General Info

Product Line	Cablofil	Finish	Electro-Galvanized Steel
UPC Number	800388247826	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Type	Accessories

Dimensions

Product Width US	3.3 in	Product Weight US	1.521 lb
Product Volume US	0.012 cu ft	Product Depth US	3.7 in
Product Height US	1.7 in		