



Cablofil
LD-6L2I-9212-12 SS304 90 OVR 12"R 12"W
Part No. P645339



Choose from an extensive selection of metallic ladder tray with a variety of rung and bottom styles to choose from. Finishes include steel, 304L and 316L stainless steel to meet the needs of any application. Rail heights range from 4" to 7" and width sizes are available up to 36".

Features & Benefits

Includes splice plates

Specifications

General Info

Product Line	Cablofil	Finish	Stainless 304
UPC Number	800388534759	Country Of Origin	Mexico
Bottom Type	Ladder	Application Sector	Commercial, Industrial
Type	Vertical Elbows		

Dimensions

Product Width US	6.0 in	Product Weight US	3.394 lb
Product Height US	4.0 in	Radius	12 in

Trade Programs

BAA	Yes
-----	-----