



Cablofil
LD-6A-ET36-2430 AL 6H HEXP TEE 36R 2430W
Part No. P645521



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

Features & Benefits

Material: Aluminum Alloy 6063 and 5052

Finish: Plain

Bottom: LD: 1" wide rung

Construction: Welded

Tray Design: Tray construction and

Connectors: All fittings are supplied with

Fitting Heights (H): 4", 5", 6", 7"

Specifications

General Info

Product Line	Cablofil	Finish	Aluminum
UPC Number	800388477902	Country Of Origin	Mexico
Bottom Type	Ladder	Application Sector	Commercial, Industrial
Type	Horizontal Other		

Dimensions

Product Width US	63.625 in	Product Weight US	27.72 lb
Product Volume US	26.197 cu ft	Product Depth US	114.0 in
Product Height US	6.241 in	Radius	36 in

Trade Programs

BAA

Yes
