



Wiremold Discontinued - PA Series 80kA SPD for sub-panel apps/Rated 120/240V Split-phase Part No. PA120T



For surge protection at the sub panel or near sensitive equipment. Designed for residential and light commercial/industrial applications. Dimensions: 6 5/16" x 4 3/4" x 3 9/16" (160mm x 120mm x 90mm). Ten-year, unconditional product warranty. Electrical Service: 120/240V, Single 0 3-Wire and Ground. Surge Protection: 80kA. NOTE: Add suffix ""-A"" to part number for NO/NC dry contact relay for connecting remote monitoring device. Add suffix ""-B"" to part number for EMI/RFI noise filter. Add ""-AB"" to part number for both options.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776005813
Country Of Origin	United States	Application Sector	Commercial
Standard	cETLus Listed: Guide VZCA	Type	Current Monitoring

Listing Agencies / 3rd Party Agencies

ETL Listed	Yes
------------	-----

Buy American Act Compliance

NAFTA	Yes
-------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Phase	1	Connection	Hard-wired
Class	75	Amperage	160 KA
Short Circuit Rating	80kA	Type of Indicators	Light

Voltage

120.0 V

Environmental Conditions

Indoor
