



Clarity SNAP™ Terminated Copper Cabling System offers the above-the-standards performance of Clarity® connectivity in a custom terminated cable assembly system that's ready to plug and go. Its innovative modular design combines high performance and installer friendly features with the quick deployment and reliability of a factory terminated and tested cabling system.

Features & Benefits

Totally modular cabling system: Dramatically faster deployment of horizontal cabling and port replication

Reduced size of cable ends: Easier cable pulling and directing through pathways and racks

Factory supplied identification: Each cable assembly includes part number and unique identifiers for traceability and association to its factory test report

Increased flexibility for MACs: Reduces total cost of ownership and allows re-use in the future (also reducing waste)

Factory-installed and tested terminations: Assembled in a controlled factory environment for consistent performance to elevated requirements confirmed by factory testing. Factory tested terminations reduce the time and cost of field testing

Clarity® 6A/10G, 6 and 5E performance: Premium performance you've come to rely on from Clarity connectivity, now in a terminated solution

Variety of options: Solutions tailored to your specific needs

Specifications

General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875000211	Country Of Origin	Mexico
Features	Pre-terminated Trunk	Application Sector	Commercial
Standard	RoHS;UL;cUL;BAA	Warranty Type	5-Year
Type	Patch Cable		

Dimensions

Product Length US	150.0 FT	Cable Length	150 ft
-------------------	----------	--------------	--------

Technical Information

Operating Temperature Min	-20 °C	Category Performance Application	Cat6a
Wire Gauge	23 AWG	Storage Humidity	0-100% RH (Non-Condensing)

Plating Specification	50 μ in Gold	Jacket Application	Riser Rated
Bend Radius	0.94 in	Shielded/Unshielded Cable	Unshielded
Conductor	4-Pair Twisted	Conductor Stranding	Solid
Operating Temperature Max	60 °C	Shield Type	F/UTP
Cable Type	Ethernet Patch Cable	Jacket Rating	LSZH
Amperage	0.96 A	Cable Diameter	0.236 in
Wattage	100 W	Connector 2	SNAP Male
Connector 1	SNAP Male	Cable Retention	25 lbF
Operating Temperature	-20°-60°C	Operating Humidity	0-100% RH (Non-Condensing)
Conductor Material	Copper	Voltage	57.0 V
Connectivity Footprint	Clarity		