



Clarity 6 angled 48-port high density Category 6 patch panel utilizes an innovative recessed angle design for a lower mounted profile. This Clarity 6 patch panel is component compliant to TIA/EIA Category 6 performance requirements. It occupies one rack unit, and measures 19" x 3.5". Jacks are grouped in six-port modules. It is part of the Clarity 6 link and channel solution that provides significant installed performance headroom.

Features & Benefits

Recessed design with lower mounted profile: Directs cords more easily to vertical management.	ETL verified to TIA Category 6 component spec: Elevated component performance.
Center tuned to Clarity 6 patch cords: More transparent mated union.	Universal wiring: Supports T568A and T568B installs.
Easy lace 110 termination: Saves installation time.	Supplied rear cable management: Supports good cabling practice.
High density design: Maximizes rack utilization.	RoHS compliant: Lead free.

Specifications

General Info

Product Line	Ortronics	Color	Black
UPC Number	662875497226	Country Of Origin	Mexico
Application Sector	Commercial/Industrial	Type	Panel

Dimensions

Product Width US	19.0 in	Product Depth US	6.1 in
Product Height US	3.5 in		

Additional Information

RoHS Conformant	Yes	Product Environmental Profile	Yes
-----------------	-----	-------------------------------	-----