



Junior Duty, Flexible Eye. Cable Diameter - 0.500-0.610-inch, Mesh Length - 8-inch, Break Strength - 1,700 lbs.

Features & Benefits

Junior-duty series grips are indispensable tools for electricians with small job requirements.

They are used to connect insulated wire bundles to pulling tape or to pull wire or rope through conduit.

Mesh Length: 8

Specifications

General Info

| | | | |
|--------------|---|--------------------|------------|
| Product Line | Pass & Seymour | Country Of Origin | Mexico |
| Construction | Support and Strain Relief Grips, Various Types of Pulling | Application Sector | Industrial |
| Standard | UL/CSA Approval (consult factory) | | |

Dimensions

| | | | |
|------------------|---------|-------------------|---------|
| Product Width US | 0.61 in | Product Length US | 12.5 in |
|------------------|---------|-------------------|---------|

Technical Information

| | | | |
|---------------------|-------------------------------|---------------------|--|
| Maximum Cable Range | 0.5 in | Minimum Cable Range | 0.61 in |
| Capacity | Various Cable Diameter Ranges | Mounting | Consult the Factory for Mounting Recommendations |
| Load | Approx. Break Strength: 1700 | | |