



Pass and Seymour  
Light Duty, Short Length, Flexible Eye  
Part No. PL1251



Light Duty, Short Length, Flexible Eye. Cable Diameter - 1.250-1.490-inch, Mesh Length - 15-inch, Break Strength - 5,800 lbs.

## Features & Benefits

Light-Duty grips are the most economical pulling grips for many applications, such as industrial plant wiring, and rewiring, and underground electrical pulls.

Mesh Length: 15

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Support and Strain Relief Grips, Various Types of Pulling	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

### Technical Information

Maximum Cable Range	1.25 in	Minimum Cable Range	1.49 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
Load	Approx. Break Strength: 5800		