



Pass and Seymour  
Light Duty, Standard Length, Flexible Eye  
Part No. PL1502

Light Duty, Standard Length, Flexible Eye. Cable Diameter - 1.500-1.990-inch, Mesh Length - 25-inch, Break Strength - 7,500 lbs.



Features & Benefits

Light-Duty grips are the most economical pulling grips for many applications, such as industrial plant wiring, and rewiring, and underground electrical pulls.

Mesh Length: 25

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Support and Strain Relief Grips, Various Types of Pulling	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

Technical Information

Maximum Cable Range	1.5 in	Minimum Cable Range	1.99 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
Load	Approx. Break Strength: 7500		