

Light Duty, Standard Length, Flexible Eye. Cable Diameter - 3.000-3.490-inch, Mesh Length - 30-inch, Break Strength - 16,200 lbs.



## Features & Benefits

Light-Duty grips are the most economical pulling grips for many applications, such as industrial plant wiring, and rewiring, and underground electrical pulls.

Mesh  
Length: 30

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007993134
Country Of Origin	Mexico	Construction	Support and Strain Relief Grips, Various Types of Pulling
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

### Technical Information

Maximum Cable Range	3 in	Minimum Cable Range	3.49 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations