



Pass and Seymour
15A, 125V Heavy Duty Spec Grade Plug Load Timer Receptacle, Black
Part No. PLT26251BK



New requirements for reducing energy consumption in commercial buildings are here. With devices that are so easy to understand, install and use, our full line of Pass and Seymour Plug Load Controllable solutions will take a load off your mind and a load off your customers electric bills.

Features & Benefits

Wire Size: #14 - #10 AWG Copper Conductor Only

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007040036	Country Of Origin	China
Application Sector	Commercial	Standard	RoHS, CSA Listed, CulUS, UL Listed, FSUL, FEDSPEC

Dimensions

Product Width US	1.73 in	Product Depth US	1.25 in
Product Height US	2.68 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Phase	Single
---------------------	--------------------------	-------	--------

Connection	Screw Terminals	Number of Wires	3
Temperature Rating	-40° - 60° C	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Environmental Conditions	UL94 V2		