



Medium Duty, Flexible Eye. Cable Diameter - 0.370-0.490-inch,  
Mesh Length - 13-inch , Break Strength - 2,600 lbs.

## Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

Mesh Length: 13

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007993530
Country Of Origin	Mexico	Construction	Support and Strain Relief Grips, Various Types of Pulling
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

### Technical Information

Maximum Cable Range	0.37 in	Minimum Cable Range	0.49 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations