



Pass and Seymour
Medium Duty, Standard Length, Flexible Eye, T-Type
Part No. PM0752



Medium Duty, Standard Length, Flexible Eye, T-Type. Cable Diameter - 0.750-0.990-inch, Mesh Length - 36-inch, Eye Diameter - 1/4-inch, Break Strength - 6,800 lbs.

Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

Mesh Length: 36: Eye Diameter: 1/4

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007185508
Country Of Origin	Mexico	Construction	Support and Strain Relief Grips, Various Types of Pulling
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)
Type	Pulling Grip		

Dimensions

Mesh Length	36 in	Cable Diameter Range	0.750-0.990 in
-------------	-------	----------------------	----------------

Technical Information

Approximate Break Strength	6800 lb	Maximum Cable Range	0.75 in
----------------------------	---------	---------------------	---------

Eye Style	Flexible	Minimum Cable Range	0.99 in
-----------	----------	---------------------	---------

Capacity

Various Cable Diameter Ranges

Indoor/Outdoor

Both

Mounting

Consult the Factory for Mounting
Recommendations
