



Pass and Seymour  
Medium Duty, Short Length, Flexible Eye, T-Type  
Part No. PM1501

Medium Duty, Short Length, Flexible Eye, T-Type. Cable Diameter - 1.500-1.990-inch, Mesh Length - 24-inch, Eye Diameter - 7/16-inch, Break Strength - 16,400 lbs.



## Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

Mesh Length: 24: Eye Diameter: 7/16

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007185218
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)
Type	Pulling Grip		

### Dimensions

Mesh Length	24 in	Cable Diameter Range	1.50-1.99 in
-------------	-------	----------------------	--------------

### Technical Information

Approximate Break Strength	16400 lb	Maximum Cable Range	1.5 in
Eye Style	Flexible	Minimum Cable Range	1.99 in

---

Capacity

Various Cable Diameter Ranges

Indoor/Outdoor

Both

---

Mounting

Consult the Factory for Mounting  
Recommendations

---