



Pass and Seymour
Medium Duty, Standard Length, Flexible Eye, T-Type
Part No. PM2002

Medium Duty, Standard Length, Flexible Eye, T-Type. Cable Diameter - 2.000-2.490-inch, Mesh Length - 36-inch, Eye Diameter - 7/16-inch, Break Strength - 18,500 lbs.



Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

Mesh Length: 36: Eye Diameter: 7/16

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007185126
Country Of Origin	Mexico	Construction	Support and Strain Relief Grips, Various Types of Pulling
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)
Type	Pulling Grip		

Dimensions

Mesh Length	36 in	Cable Diameter Range	2.00-2.49 in
-------------	-------	----------------------	--------------

Technical Information

Approximate Break Strength	18500 lb	Maximum Cable Range	2 in
Eye Style	Flexible	Minimum Cable Range	2.49 in

Capacity

Various Cable Diameter Ranges

Indoor/Outdoor

Both

Mounting

Consult the Factory for Mounting
Recommendations
