



Pass and Seymour
Medium Duty, Standard Length, Flexible Eye, T-Type
Part No. PM3502

Medium Duty, Standard Length, Flexible Eye, T-Type. Cable Diameter - 3.500-3.990-inch, Mesh Length - 40-inch, Eye Diameter - 5/8-inch, 31,000 lbs.



Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

Mesh Length: 40: Eye Diameter: 5/8

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007185331
Country Of Origin	Mexico	Construction	Support and Strain Relief Grips, Various Types of Pulling
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)
Type	Pulling Grip		

Dimensions

Mesh Length	40 in	Cable Diameter Range	3.50-3.99 in
-------------	-------	----------------------	--------------

Technical Information

Approximate Break Strength	31000 lb	Maximum Cable Range	3.5 in
Eye Style	Flexible	Minimum Cable Range	3.99 in

Capacity

Various Cable Diameter Ranges

Indoor/Outdoor

Both

Mounting

Consult the Factory for Mounting
Recommendations
