



**Wiremold  
Plugmold Tough Power Strip with Diamond Plate Cover**  
Part No. PM48TC



They don't just look tough. They are tough. Plugmold Tough Power Strips are easy to handle and easy to install. Genuine diamond-plate aluminum looks great on workbenches, in garages, or anywhere you need to access up to 10 power outlets.

## Features & Benefits

Diamond Plate Aluminum: looks great on workbenches or in garages  
Easy to handle and install  
Phillips head screwdriver

Up to 10 power outlets and circuit breaker protection  
6' cord  
Tools needed for installation:  
Tape measure

## Specifications

### General Info

Product Line	Wiremold	Color	Silver
UPC Number	086698000331	Country Of Origin	China
Material	Steel	Product Series	PM Series
Number of Receptacles	5	Application Sector	Commercial, Education, Entertainment, Healthcare, Hospitality, Retail
Standard	cULus Listed Relocatable Power Tap: File E66421 Guide XBYS/XBYS7	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Plugmold	Installed Devices	Duplex Receptacle

---

## Dimensions

---

Product Width US	2.006 in	Product Weight US	4.65 lb
Product Volume US	110.74 cu in	Product Depth US	1.13 in
Product Height US	1.25 in	Product Length US	48.0 in
Receptacle Spacing	9 in		

---

## Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

## Additional Information

---

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

---

## Technical Information

---

Is Pre-Wired	Yes	Wiring Configuration	Single Circuit
Cord Length	6 ft	Amperage	15 A
Indoor/Outdoor	Indoor	Wiring Method	Cord-ended
NEMA Configuration Code	5-15R	Mounting Type	On Surface
Voltage	125.0 V		

---