



Pass and Seymour
800 Series Cable Reel with Tri-Tap, 40FT, 12AWG, 15A
Part No. CR08123N40T15



Delivers simple, reliable power distribution with 40 feet of reach and clear illuminated NEMA 5-15 tri-tap connector, making it easy to support multiple connections and confirm power at a glance. Built with a durable, lightweight nonmetallic enclosure and a detachable rotating mounting bracket, it installs quickly and performs in everyday applications. Designed as a streamlined, single-SKU solution, the 800 Series Cable Reel reduces complexity while meeting core performance needs in data centers, education and light commercial spaces.

Features & Benefits

Clear illuminated NEMA 5-15 triple tap
12/3 SJTW yellow cord, 105C rated
15A push button breaker in reel housing

Rugged nonmetallic enclosure
2ft incoming cord with NEMA 5-15 plug
Detachable rotating mounting bracket

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	China	Features	Illuminated, Retractable
Application Sector	Commercial	Warranty Type	1-Year
Type	Cable Reel		

Dimensions

Product Depth US	6.0 in	Product Height US	15.5 in
Product Length US	14.0 in		

Listing Agencies / 3rd Party Agencies

ETL Listed	Yes
------------	-----

Additional Information

Energy Savings	No
----------------	----

Technical Information

Wire Gauge	12 AWG	Cord Length	40 ft
Amperage	15 A	Number of Conductors	3
Indoor/Outdoor	Indoor	Mobile End	Triple Tap
Operating Temperature	-10°-40°C	Voltage	125.0 V