Pass and Seymour

# Pin & Sleeve Connector 5W 100A 200/346 240/415V 1¼" Liquid-Tight Fitting

Part No. LE5100C6WNPT12A



100A Pin & Sleeve Connector for use in demanding environments such as data centers, manufacturing facilities, entertainment and more. Configuration includes an NPT Liquid-Tight Fitting for seamless installation with conduit or MC cable. UL Certified to IEC 309 standards.

## Features & Benefits

Legrand Pin & Sleeve products provide installation ease, enduring performance in harsh conditions and guaranteed IEC 309 compatibility.

Locking ring with an integral neoprene gasket provides watertight seal when plug and connector/receptacle are mated.

Integral NPT Liquid-Tight fitting provides seamless installation ease in applications such as data centers.

Standard clocking positions identified by device color allow for quick identification and intermateability.

Shrouded, nickel-plated, solid brass pins provide corrosion protection and excellent conductivity.

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Pass & Seymour | Color | Gray |
| UPC Number | 785007517965 | Country Of Origin | United States |
| Material | Nylon | Features | Watertight |
| Application Sector | Data Center, Industrial | Warranty Type | 1-Year |

### Dimensions

| | | | |
|---|---|---|---|
| Product Width US | 5.3 in | Product Height US | 5.2 in |
| Product Length US | 14.3 in | | |

### Additional Information

| | |
|---|---|
| Energy Savings | No |

## Technical Information

| | | | |
|---|---|---|---|
| Connector Style | Pin & Sleeve | Flanged | No |
| Phase | Single | Terminal Accommodation | #6 AWG -#1/0 AWG |
| Number of Wires | 5 | Amperage | 100 A |
| Indoor/Outdoor | Both | Voltage | 200/346 V, 240/415 V |