Pass and Seymour

Pin & Sleeve Connector 5W 100A 277/480V

Part No. LE5100C7W



100A Pin & Sleeve Connector for use in demanding environments such as data centers, manufacturing facilities, entertainment and more. Configuration includes cord clamp. UL Certified to IEC 309 standards.

Features & Benefits

Legrand Pin & Sleeve products provide installation ease, enduring performance in harsh conditions and guaranteed IEC 309 compatibility.

Locking ring with an integral neoprene gasket provides watertight seal when plug and connector/receptacle are mated.

Cord clamp fitting provides seamless installation ease in applications such as data centers.

Standard clocking positions identified by device color allow for quick identification and intermateability.

Shrouded, nickel-plated, solid brass pins provide corrosion protection and excellent conductivity.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007517972	Country Of Origin	United States
Material	Nylon	Features	Watertight
Application Sector	Data Center, Industrial	Warranty Type	1-Year

Dimensions

Product Width US	5.3 in	Product Height US	5.2 in
Product Length US	14.3 in		

Additional Information

Energy Savings	No

Technical Information

Connector Style	Pin & Sleeve	Flanged	No
Phase	Single	Terminal Accommodation	#6 AWG -#1/0 AWG
Number of Wires	5	Amperage	100 A
Indoor/Outdoor	Both	Voltage	277/480 VAC