Pass and Seymour

Pin & Sleeve Connector 5W 100A 277/480V 1¼" Liquid-Tight Fitting

Part No. LE5100C7WNPT12A



100A Pin & Sleeve Connector for use in demanding environments such as data centers, manufacturing facilities, entertainment and more. Configuration includes an NPT Liquid-Tight Fitting for seamless installation with conduit or MC cable. UL Certified to IEC 309 standards.

Features & Benefits

Legrand Pin & Sleeve products provide installation ease, enduring performance in harsh conditions and guaranteed IEC 309 compatibility.

Locking ring with an integral neoprene gasket provides watertight seal when plug and connector/receptacle are mated.

Integral NPT Liquid-Tight fitting provides seamless installation ease in applications such as data centers.

Standard clocking positions identified by device color allow for quick identification and intermateability.

Shrouded, nickel-plated, solid brass pins provide corrosion protection and excellent conductivity.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007517989	Country Of Origin	United States
Material	Nylon	Features	Watertight
Application Sector	Data Center, Industrial	Warranty Type	1-Year

Dimensions

Product Width US	5.3 in	Product Height US	5.2 in
Product Length US	14.3 in		

Additional Information

Energy Savings	No

Technical Information

Connector Style	Pin & Sleeve	Flanged	No
Phase	Single	Terminal Accommodation	#6 AWG -#1/0 AWG
Number of Wires	5	Amperage	100 A
Indoor/Outdoor	Both	Voltage	277/480 VAC